

The magnification mirror magnifies your face to the details and is suitable to care keratin plugs, mottles and wrinkles on your skin.

CLIP MIRROR 3x 5x

Add the mirror to your daily-use mirror...



For base makeup...

The position of the clip mirror can be adjusted not to disturb your makeup.



For checking the detail of your makeup...

The mirror can be set at the position convenient for checking the detail of your makeup, such as eye makeup.



At the washstand...



Convenient for your makeup at the washstand



The photo shows an image of reflection in the magnification mirror.

Add the magnification mirror for your makeup.

CLIP MIRROR 2type


3x and 5x magnification mirrors, now on sale!

PC-03

PC-05



3x magnification mirror



5x magnification mirror



The magnification mirror adds much convenience to your daily-use mirror and washstand mirror.

The position, slant and direction of the clip are adjustable for your use.



The mirror can be tilted upward and downward.



The shaft can be turned upward and downward.



The mirror can be turned right and left.



The clip can grip an edge having a thickness of 25 mm or less.




Nonslip and nonabrasive Elastomer clip

90-mm-diameter round mirror



Two variants of magnification, 3x and 5x

Reflected images in a plain mirror and magnification mirror



Plain mirror

3x

5x

Image of the curvature of the mirror



3x(600R)

5x(400R)

Usage and precautions for use

●At first, move your face close to the magnification mirror and then move away from the mirror to find the focal point you can see clearly reflected image. ●A mirror of greater curvature has shorter focal length, in other words, you can see a clear image nearer to the mirror surface. ●A high-magnification mirror gives vague image outside the focal point. ●Do not look at the magnified image too long. It may cause eyestrain or make you feel sick.

*Images are magnified in concave mirrors and enlarged more with the increase of their curvature. The magnification of our mirrors is roughly indicated by the radius of curvature (abbreviated as "R") of the mirrors. A magnification mirror having smaller radius of curvature (R) has greater curvature, in other words, reflects a larger image.

*The magnification mirrors may focus the sun's rays to burn up a combustible material and cause fire. So do not use or store the magnification mirrors under direct sunlight.

*Magnification mirror without a plain mirror.

ONE PLUS CLIP MIRROR 3x 5x

Product name	Item Code.	Suggested retail price	Size	Color	JAN	Quantity per carton	Material
3x CLIP MIRROR	PC-03	¥1,300 and tax	[Product](Frame)95-mm-diameter round (Mirror)glass mirror:90-mm-diameter round mirror (Clip)length135mm,width25mm [Package]100mm×50mm×180mm(Package)	White	773562	72	Frame: ABS resin, Mirror: glass mirror Clip: ABS resin, polyacetal, polycarbonate, steel, elastomer Double-sided tape: polyurethane
5x CLIP MIRROR	PC-05	¥1,400 and tax	[Weight]61g(Net weight) / 97g(Gross weight)		773579		

*Do not give impact to the mirrors by dropping off, etc. Impacted mirrors may break and hurt the user. *The metal parts of the mirrors are deteriorated when stored at high temperature and humidity for a long time. *Chemicals sticking on the mirrors must be wiped off with dry cloth.

*Each of the "JAN codes" given in six digits in this catalogue constitutes the product code and check digit, and follows the code, 4510510 indicating the country and manufacturer codes.