

For Enjoying Your Life

ACTIVE-LIFE
MIRROR

NEW!

Safe and secure break-proof

For Enjoying Your Life

ACTIVE-LIFE MIRROR



Break-proof mirror improves your QOL (quality of life).

Old ladies often stop wearing makeup because of "sickness" or "infrequent chances of going out". The ladies wearing no makeup are apt to stay home and have fewer chances of meeting their friends. Such lifestyle increases the possibility of losing their health to the serious level requiring nursing care. Makeup gives them a proper feeling of tension and cheers them up to cause change in their attitude, such as gaining confidence to meet people. It has already been proved that application of makeup stimulates the brains of the wearers and exercises their fingers, arms and other parts of their body to make a good effect on their hearts, brains and bodies so as to keep or improve their ADL (activities of daily living) and consequently improve their QOL (quality of life). We, Horiuchi Mirror Industry Co., Ltd., have developed and manufactured complete makeup mirrors with a break-proof polyester resin mirror to provide enjoyable makeup to elderly people and those who require nursing care. The "ACTIVE-LIFE MIRROR" does not break when falling off a table or hand, and can be used safely by anyone.

Makeup gives good effect to

Your heart

Make you
feel better

Your brain

Activate
your brain

your body

Improve your
physical function

For keeping and improving your ADL (activities of daily living)

For keeping and improving your QOL (quality of life)



IK-01



IK-02



IK-03



IK-04

Once it is sold out we will have no more, and will not make any more.



IK-05

Safe and secure, break-proof ACTIVE-LIFE MIRROR

Product name	Item	Suggested retail price	JAN	Quantity per carton	Size·Weight	Material
ACTIVE-LIFE Professional Model MIRROR(M)	IK-01	¥2,200 and tax	773760	48	[Product] Size: 125mm×175mm×15mm Weight: 170g [Bag] Size: 140mm×220mm×20mm Weight: 180g	[Frame]EVA resin [Mirror]PET film mirror (with vapor-deposited aluminum layer), PS resin, Aluminum, Foamed PE resin
ACTIVE-LIFE Professional Model MIRROR(LL)	IK-02	¥4,000 and tax	773777	24	[Product] Size: 185mm×280mm×15mm Weight: 420g [Bag] Size: 215mm×325mm×20mm Weight: 440g	[Frame]EVA resin [Mirror]PET film mirror (with vapor-deposited aluminum layer), PS resin, Aluminum, Foamed PE resin
ACTIVE-LIFE Professional Model MIRROR(3L)	IK-03	¥5,000 and tax	773784	24	[Product] Size: 255mm×320mm×15mm Weight: 630g [Bag] Size: 280mm×360mm×20mm Weight: 650g	[Frame]EVA resin [Mirror]PET film mirror (with vapor-deposited aluminum layer), PS resin, Aluminum, Foamed PE resin
ACTIVE-LIFE Stand Mirror	IK-04	¥3,000 and tax	773791	36	[Product] Size: 198mm×242mm×20mm Weight: 370g [Bag] Size: 220mm×300mm×25mm Weight: 395g	[Frame]PS resin [Mirror]PET film mirror (with vapor-deposited aluminum layer), PS resin, Aluminum, Foamed PE resin
ACTIVE-LIFE Hand Mirror	IK-05	¥1,700 and tax	773807	48	[Product] Size: 140mm×263mm×10mm Weight: 150g [Bag] Size: 160mm×280mm×15mm Weight: 170g	[Frame]PS resin [Mirror]PET film mirror (with vapor-deposited aluminum layer), PS resin, Aluminum, Foamed PE resin

- The hardcoated mirror surface may be damaged by hard materials such as wire wool.
- Do not contact the mirror with organic solvents such as benzene and paint thinners.
- Acidic or alkaline chemicals, such as mold removers and bleaches deteriorate or tarnish the mirror. When the mirror is stained with the chemicals, immediately wipe them off.
- Wipe off the stain on the mirror lightly with cloth moistened with a mild detergent.
- Be careful not to injure your hands at the edges of the mirror while cleaning the mirror.
- Do not expose the mirror to high temperature above 70 °C that causes the deformation of the mirror.
- The polyester resin mirror has slight flexure, which is not found on glass mirror, though it is inevitable due to the properties of polyester resin.

Lightweight



The polyester resin mirror weighs about 23 % lighter than a glass mirror to make the products lighter. So the ACTIVE-LIFE MIRROR can be easily and safely taken anywhere.

Easy makeup



The slant of the mirror is adjustable to the best position for makeup.

Break-proof




The impact-resistant PET resin makes the mirrors break-proof and safe. Safe and secure when you drop the mirror.

Scratch-resistant



The mirror is hardcoated and can be cleaned by the usual way for glass mirrors, such as wiping with cloth.

■Cross section of the mirror



■Material of the mirror

PET film mirror (with vapor-deposited aluminum layer)
PS resin
Aluminum
Foamed PE resin